

SECHSBEIN - with plastic foot

Description

Special spacer with formwork protector for use with component activation. Low demand because of the large support circle of approx. 410 mm. Alternatively possible with crossbar.

Application


The Sechsbein are positioned directly on the formwork. The pipes for component activation are then attached to the Sechsbein. The usability of the product in the respective installation situation must be checked by the user! Further information on the arrangement and installation distances can be found in the relevant DBV leaflets.

Material

- Steel
- Free from PVC, CFC and HFC
- Without substances of very high concern according to ECHA candidate list (REACH Regulation)


Packaging

- Free of halogen-containing compounds, azo dyes, flame retardants



SECHSBEIN - with plastic foot

Item no.	Height mm	Ø support circle mm	Ø Iron mm	Pcs/ PU
LSB05KF	50	≈ 410	6	50
LSB06KF	60	≈ 410	6	50
LSB07KF	70	≈ 410	6	50
LSB08KF	80	≈ 410	6	50
LSB09KF	90	≈ 410	6	50
LSB10KF	100	≈ 410	6	50
LSB11KF	110	≈ 410	6	50
LSB12KF	120	≈ 410	6	50
LSB13KF	130	≈ 410	6	50
LSB14KF	140	≈ 410	6	50
LSB15KF	150	≈ 410	6	50
LSB16KF	160	≈ 410	6	50
LSB17KF	170	≈ 410	6	50
LSB18KF	180	≈ 410	6	50
LSB19KF	190	≈ 410	6	50
LSB20KF	200	≈ 410	6	50



Tested according to DBV leaflet „Unterstützungen“.

Nevoga Group

FREILASSING | DE 

ZNOJMO | CZ 

BIESIEKIERZ | PL 

 MADE IN EUROPE

info@nevoga.com

www.nevoga.com



All information has been prepared to the best of our knowledge and according to the current state of the art. However, Nevoga does not guarantee the accuracy and completeness of the information. This data sheet is updated on an ongoing basis. Nevoga therefore reserves the right to make changes without prior notice to the customer. The latest version can be found at www.nevoga.com.

<https://www.nevoga.com/en/product/sechsbein-with-plastic-foot/>

Created: 30.10.2023

Page 2 / 2